



## Messenger Stainless Steel Cable Tie for RCT RADIAX® Radiating cables

## Product Classification

**Product Type** Cable tie

## Dimensions

**Nominal Size** 1-1/4 in | 1-5/8 in | 1/2 in | 7/8 in  
**Compatible Diameter, maximum** 102.000 mm | 4.016 in  
**Height** 5.10 mm | 0.20 in  
**Length** 362.00 mm | 14.25 in  
**Width** 7.90 mm | 0.31 in

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

**Hanger Type** Cable tie  
**Cables per Hanger** 1  
**Material Type** Stainless steel  
**Package Quantity** 1

## Mechanical Specifications

**Flammability Test Method** UL 2043  
**Mounting** Messenger wire  
**Pullout Force, maximum with no cable slippage** 700 N | 157 lbf

## Packed Dimensions

**Shipping Weight** 0.01 kg | 0.02 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

