



SnapStak® Hanger for 7/8 in coaxial cable, quadruple stack capability, includes reinforcement bar

Product Classification

Brand	SnapStak®
Product Type	Hanger kit

Dimensions

Nominal Size	7/8 in
Compatible Diameter, maximum	30.988 mm 1.220 in
Compatible Diameter, minimum	26.670 mm 1.050 in
Height	41.00 mm 1.61 in
Length	64.00 mm 2.52 in
Width	40.00 mm 1.57 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Snap-in hanger
Cables per Hanger	1
Color	Silver
Material Type	Stainless steel
Maximum Stack Height	4
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

SSH-78-4

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	3/4 in drilled cable ladder
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	15.6 cm 6.1 in
Length	10.8 cm 4.3 in
Shipping Weight	0.42 kg 0.93 lb
Width	14.8 cm 5.8 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power