



## Flex-Twist Hanger Assembly for WR90

### Product Classification

**Product Type** Hanger kit

### Dimensions

**Height** 57.00 mm | 2.24 in  
**Length** 800.00 mm | 31.50 in  
**Waveguide Size** WR90 | WG16 | R100  
**Width** 127.00 mm | 5.00 in

### Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

### General Specifications

**Hanger Type** Flex-Twist hanger  
**Cable Type** Elliptical waveguide  
**Cables per Hanger** 1  
**Color** Silver  
**Includes** Clamp | Rubber grommet | Threaded rod  
**Material Type** Stainless steel  
**Package Quantity** 1

### Mechanical Specifications

**Corrosion Test Method** MIL-STD-889B | MIL-F-14072C  
**Mounting** 4.5 in OD pipe  
**Wind Velocity Survival Rating with 1/2 in (12 mm) Radial Ice** 201 km/h | 125 mph

### Packed Dimensions

**Shipping Weight** 0.06 kg | 0.12 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

