



Double Hanger Kit for 7/8 in coaxial cable, triple stack; includes hardware and angle adapter

## Product Classification

<b>Brand</b>	ValuSite™
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Nominal Size</b>	7/8 in
<b>Compatible Diameter, maximum</b>	28.194 mm   1.110 in
<b>Compatible Diameter, minimum</b>	26.670 mm   1.050 in
<b>Height</b>	20.70 cm   8.15 in
<b>Length</b>	3.77 cm   1.48 in
<b>Width</b>	2.61 cm   1.03 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Composite clamp
<b>Cables per Hanger</b>	6
<b>Color</b>	Black
<b>Harmonized System (HS) Code</b>	854420 (Coaxial cable and other coaxial electric conductors)
<b>Includes</b>	Angle adapter   Hardware
<b>Material Type</b>	Engineered plastic   Stainless steel
<b>Maximum Stack Height</b>	3
<b>Ordering Note</b>	CommScope® standard product in Europe, the Middle East, and Africa   CommScope® standard product in Mexico, Central America, and South America

# DHK-78-6-P

---

**Package Quantity** 1

## Mechanical Specifications

**Corrosion Resistance, minimum with no degradation**  $\geq 500$  hours in salt spray chamber  
**Mounting** M8 hardware  
**UV Resistance, minimum with no degradation**  $\geq 100$  hours exposure in accelerated UV life chamber  
**Vibration Survival**  $\geq 4$  hours at resonant frequency  
**Environmental Strength Capability** Double cable weight

## Packed Dimensions

**Height** 20.3 cm | 8.0 in  
**Length** 15.2 cm | 6.0 in  
**Shipping Weight** 0.27 kg | 0.60 lb

## Included Products

Angle Adapter (Product Component—not orderable) — Angle Adapter

Hardware (Product Component—not orderable) — Hardware

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power