

Double Hanger Kit for 1/2 in coaxial cable, triple stack; includes hardware and angle adapter



Product Classification

Brand	ValuSite™
Product Type	Hanger kit

Dimensions

Nominal Size	1/2 in
Compatible Diameter, maximum	16.256 mm 0.640 in
Compatible Diameter, minimum	15.240 mm 0.600 in
Height	78.00 mm 3.07 in
Length	66.08 mm 2.60 in
Width	25.82 mm 1.02 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Composite clamp
Cables per Hanger	6
Color	Black
Includes	Angle adapter Hardware
Material Type	Engineered plastic Stainless steel
Maximum Stack Height	3
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa CommScope® standard product in Mexico, Central America, and South America
Package Quantity	1

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	M8 hardware
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	30.4 cm 12.0 in
Length	2.5 cm 1.0 in
Shipping Weight	0.46 kg 1.01 lb
Width	27.9 cm 11.0 in

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power