



Flex-Twist Hanger Assembly for WR187

Product Classification

Product Type Hanger kit

Dimensions

Height 387.35 mm | 15.25 in

Length 387.35 mm | 15.25 in

Waveguide Size WR187 | WG12 | R48

Width 82.55 mm | 3.25 in

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Flex-Twist hanger

Cable Type Elliptical waveguide

Cables per Hanger 1

Color Silver

Includes Clamp | Rubber grommet | Threaded rod

Material Type Stainless steel

Package Quantity 1

Mechanical Specifications

Corrosion Test Method MIL-STD-889B | MIL-F-14072C

Mounting 4.5 in OD pipe

Wind Velocity Survival Rating with 1/2 in (12 mm) Radial Ice 201 km/h | 125 mph

Packed Dimensions

Shipping Weight 0.68 kg | 1.50 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

