



Butterfly Hanger for 5 in coaxial cable and elliptical waveguide 20

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size	5 in
Compatible Diameter, maximum	132.080 mm 5.200 in
Compatible Diameter, minimum	127.000 mm 5.000 in
Height	42.00 mm 1.65 in
Length	63.50 mm 2.50 in
Width	38.10 mm 1.50 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type	Standard butterfly hanger
Cable Type	Corrugated
Cables per Hanger	1
Color	Silver
Material Type	Galvanized steel
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	1/2 in threads
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	36.8 cm 14.5 in
Length	11.0 cm 4.3 in
Shipping Weight	2.11 kg 4.65 lb
Width	11.0 cm 4.3 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

