

# FA-17MM-114-RM



1 1/4 in Double Hanger Kit for HELIAX® FiberFeed® Direct Power tails, 17 mm grommet, round member adapter (75-100 mm), clamp head, triple stack, kit of 10

## Product Classification

<b>Brand</b>	FiberFeed®   HELIAX®
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Compatible Diameter, maximum</b>	17.000 mm   0.669 in
<b>Compatible Diameter, minimum</b>	17.000 mm   0.669 in
<b>Height</b>	184.32 mm   7.26 in
<b>Length</b>	120.46 mm   4.74 in
<b>Width</b>	28.60 mm   1.13 in

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Composite clamp
<b>Cables per Hanger</b>	6
<b>Color</b>	Black
<b>Material Type</b>	Corrosion proof coated metal   Engineered plastic
<b>Maximum Stack Height</b>	3
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	M8 hardware
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

# FA-17MM-114-RM

---

## Included Products

DHK-114-6-P — Double Hanger Kit for 1-1/4 in coaxial cable, triple stack; includes hardware and angle adapter

HG-58-114 — Grommet with 19mm hole for 1-1/4 in SnapStak or polymer block hanger

MF39901-10 — Clamp Head

31670-3 — Round Member Adapter for 3–4 in round members

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power