

19256B-C



Lace-up Hoisting Grip with tie wraps for HELIAX® FiberFeed® cables

Product Classification

Product Type Hoisting grip

Dimensions

Nominal Size 7/8 in
Grip Length, minimum 431.80 mm | 17.00 in
Leader Length, minimum 330.20 mm | 13.00 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Lace-up hoisting grip
Attachment Spacing Intervals 61 m | 200 ft
Material Type Stainless steel
Ordering Note CommScope® non-standard product
Package Quantity 1
Support Clamp Not included
Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 500 lb

Packed Dimensions

Height 3.8 cm | 1.5 in
Length 22.2 cm | 8.7 in
Width 21.8 cm | 8.6 in
Shipping Weight 0.22 kg | 0.49 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)

