

SHK-78-2-P

Single Hanger Kit for 7/8 in coaxial cable, double stack; includes hardware and angle adapter



Product Classification

Brand	ValuSite™
Product Type	Hanger kit

Dimensions

Nominal Size	7/8 in
Compatible Diameter, maximum	28.194 mm 1.110 in
Compatible Diameter, minimum	26.670 mm 1.050 in
Height	101.60 mm 4.00 in
Length	60.09 mm 2.37 in
Width	26.21 mm 1.03 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Composite clamp
Cables per Hanger	2
Color	Black
Harmonized System (HS) Code	854420 (Coaxial cable and other coaxial electric conductors)
Includes	Angle adapter Hardware
Material Type	Engineered plastic Stainless steel
Maximum Stack Height	2
Ordering Note	CommScope® standard product in Asia Pacific CommScope® standard product in Mexico, Central America, and South America
Package Quantity	1

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	M8 hardware
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	15.0 cm 5.9 in
Length	3.0 cm 1.2 in
Shipping Weight	0.45 kg 1.00 lb
Width	15.0 cm 5.9 in

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power