

SSH-XL



SnapStak® Plus Adjustable Hanger for 36mm to 51mm Cable - No Grommets Required. For patents, see www.cs-pat.com.

Product Classification

Brand	SnapStak® Plus
Product Type	Hanger kit

Dimensions

Compatible Diameter, maximum	51.000 mm 2.008 in
Compatible Diameter, minimum	36.000 mm 1.417 in
Height	88.00 mm 3.46 in
Length	99.00 mm 3.90 in
Width	41.00 mm 1.61 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Snap-in hanger
Accessories	Hangers
Cables per Hanger	1
Color	Silver
Material Type	Stainless steel
Maximum Stack Height	2
Maximum Stack Height, Coaxial	2
Ordering Note	CommScope® standard product in the United States and Canada
Package Quantity	10
Patent Number	US 9,866,004

SSH-XL

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	=1000 hours in salt spray chamber
Flammability Test Method	UL 2043
Mounting	3/4 in drilled cable ladder
Vibration Survival	=4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	304.8 mm 12.0 in
Length	254.0 mm 10.0 in
Shipping Weight	0.53 kg 1.17 lb
Width	15.0 cm 5.9 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power