

SHK-19-1-P-10



Hanger Kit for single stack of RFF cable; includes ten sets of hardware, angle adapters and rubber grommets

Product Classification

Brand	HELIAX®
Product Type	Hanger kit

Dimensions

Compatible Diameter, maximum	19.558 mm 0.770 in
Compatible Diameter, minimum	20.066 mm 0.790 in
Height	42.00 mm 1.65 in
Length	171.00 mm 6.73 in
Width	60.00 mm 2.36 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Composite clamp
Cables per Hanger	1
Color	Black
Includes	Angle adapter Hardware Rubber grommet
Material Type	Engineered plastic EPDM rubber Stainless steel
Maximum Stack Height	1
Package Quantity	10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
--	----------------------------------

SHK-19-1-P-10

Mounting	M8 hardware
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	0.0 cm 0.0 in
Length	0.0 cm 0.0 in
Shipping Weight	2.80 kg 6.17 lb
Width	0.0 cm 0.0 in

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power