



Jackmoon BEST-Link High Compression Conduit Coupler, Size 1.00, for conduits with outer diameter between 31.50 and 34.80 mm, black

- Feature a patented dual-action sealing system that stops air flow in two places at the coupling joint
- Corrosion-proof, light-weight, low profile, and low cost
- Provides for a greater range of application per nominal size, reducing mismatching of products in the field.
- Air-tight and water-tight coupling or splicing of conduits and innerducts reduces cable pulling and blowing resistance
- Suited for high-pressure (125 psi maximum) cable propulsion deployments

Product Classification

Brand	Jackmoon®
Product Type	Conduit coupler, high compression
Product Series	BEST-Link

Dimensions

Conduit Outer Diameter, maximum	34.80 mm		1.37 in
Conduit Outer Diameter, minimum	31.50 mm		1.24 in
Nominal Size	1 in		

General Specifications

Color	Black
--------------	-------

Material Specifications

Material Type	All plastic construction
----------------------	--------------------------

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

