



Jackmoon Anodized Aluminum Conduit Coupler, Size 0.75, for conduits with diameter between 23.10 and 27.40 mm, reverse threaded, black

- Anodized coating is color-coded for easy size identification
- Ribbed external surface provides excellent non-slip gripping during installation
- Low profile design allows the couplers to pass easily through plowchutes
- Designed for all types of polyethylene ducts

Product Classification

Brand	Jackmoon®
Product Type	Conduit coupler, aluminum

Dimensions

Conduit Outer Diameter, maximum	27.40 mm 1.08 in
Conduit Outer Diameter, minimum	23.10 mm 0.91 in
Nominal Size	3/4 in

General Specifications

Color	Black
--------------	-------

Material Specifications

Material Type	Anodized aluminum
----------------------	-------------------

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

