



Jackmoon Anodized Aluminum Conduit Coupler, Size 1.00/1.25, for conduits with diameter between 35.60 and 39.90 mm to conduits with diameter between 30.30 and 36.00 mm, reducer, aluminum

- Anodized coating is color-coded for easy size identification
- Ribbed external surface provides excellent non-slip gripping during installation
- Low profile design allows the couplers to pass easily through plowchutes
- Designed for all types of polyethylene ducts

Product Classification

Brand Jackmoon®
Product Type Conduit coupler, aluminum

Dimensions

Conduit Outer Diameter, maximum 39.90 mm | 1.57 in
Conduit Outer Diameter, minimum 35.60 mm | 1.40 in
Nominal Size 1 in

General Specifications

Color Aluminum

Material Specifications

Material Type Anodized aluminum

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

