



Jackmoon Anodized Aluminum Conduit Coupler, Size 1.125, for conduits with diameter between 35.60 and 39.90 mm, reverse threaded, green

- Anodized coating is color-coded for easy size identification
- Ribbed external surface provides excellent non-slip gripping during installation
- Low profile design allows the couplers to pass easily through plowchutes
- Designed for all types of polyethylene ducts

Product Classification

Brand	Jackmoon®
Product Type	Conduit coupler, aluminum

Dimensions

Conduit Outer Diameter, maximum	39.90 mm 1.57 in
Conduit Outer Diameter, minimum	35.60 mm 1.40 in
Nominal Size	1-1/4 in

General Specifications

Color	Green
--------------	-------

Material Specifications

Material Type	Anodized aluminum
----------------------	-------------------

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

