



Jackmoon Anodized Aluminum Conduit Coupler, Size 1.25, for conduits with diameter between 37.60 and 43.20 mm, reverse threaded, bergundy

- Anodized coating is color-coded for easy size identification
- Ribbed external surface provides excellent non-slip gripping during installation
- Low profile design allows the couplers to pass easily through plowchutes
- Designed for all types of polyethylene ducts

Product Classification

Brand Jackmoon®
Product Type Conduit coupler, aluminum

Dimensions

Conduit Outer Diameter, maximum 43.20 mm | 1.70 in
Conduit Outer Diameter, minimum 37.60 mm | 1.48 in
Nominal Size 1-1/4 in

General Specifications

Color Bergundy

Material Specifications

Material Type Anodized aluminum

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

