



Jackmoon Anodized Aluminum Conduit Coupler, Size 1.25/1.50, for conduits with diameter between 35.60 and 39.90 mm to conduits with diameter between 41.18 and 48.26 mm, reducer, blue

- Anodized coating is color-coded for easy size identification
- Ribbed external surface provides excellent non-slip gripping during installation
- Low profile design allows the couplers to pass easily through plowchutes
- Designed for all types of polyethylene ducts

Product Classification

Brand Jackmoon®
Product Type Conduit coupler, aluminum

Dimensions

Conduit Outer Diameter, maximum 39.90 mm | 1.57 in
Conduit Outer Diameter, minimum 35.60 mm | 1.40 in
Nominal Size 1-1/4 in

General Specifications

Color Dark blue

Material Specifications

Material Type Anodized aluminum

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

