



Jackmoon Anodized Aluminum Conduit Coupler, Size 1.50, for conduits with diameter between 45.70 and 50.80 mm, reverse threaded, navy blue

- Anodized coating is color-coded for easy size identification
- Ribbed external surface provides excellent non-slip gripping during installation
- Low profile design allows the couplers to pass easily through plowchutes
- Designed for all types of polyethylene ducts

Product Classification

Brand Jackmoon®
Product Type Conduit coupler, aluminum

Dimensions

Conduit Outer Diameter, maximum 50.80 mm | 2.00 in
Conduit Outer Diameter, minimum 45.70 mm | 1.80 in
Nominal Size 1-1/2 in

General Specifications

Color Navy blue

Material Specifications

Material Type Anodized aluminum

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

