



Jackmoon Anodized Aluminum Conduit Coupler, Size 2.00, for conduits with diameter between 58.70 and 63.80 mm, reverse threaded, bronze

- Anodized coating is color-coded for easy size identification
- Ribbed external surface provides excellent non-slip gripping during installation
- Low profile design allows the couplers to pass easily through plowchutes
- Designed for all types of polyethylene ducts

Product Classification

Brand Jackmoon®
Product Type Conduit coupler, aluminum

Dimensions

Conduit Outer Diameter, maximum 63.80 mm | 2.51 in
Conduit Outer Diameter, minimum 58.70 mm | 2.31 in
Nominal Size 2 in

General Specifications

Color Bronze

Material Specifications

Material Type Anodized aluminum

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

