



Jackmoon Threaded TUFF-Link Conduit Coupler, Size 1.25, for conduits with outer diameter between 39.40 and 40.40 mm, gray

- Designed for both press-on and thread-on airtight connections of smooth walled and ribbed HDPE duct and inner duct
- Features high tensile strength plastic with exceptional resistance to side load pressure for maximum durability
- Air-tight and water-tight coupling or splicing of conduits and inner ducts reduces cable pulling and blowing resistance
- Recommended that couplers are installed with the hydraulic coupling press

## Product Classification

<b>Brand</b>	Jackmoon®
<b>Product Type</b>	Conduit coupler, threaded
<b>Product Series</b>	TUFF-Link

## Dimensions

<b>Conduit Outer Diameter, maximum</b>	40.40 mm   1.59 in
<b>Conduit Outer Diameter, minimum</b>	39.40 mm   1.55 in
<b>Nominal Size</b>	1-1/4 in

## General Specifications

<b>Color</b>	Gray
--------------	------

## Material Specifications

<b>Material Type</b>	All plastic construction
----------------------	--------------------------

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

