



Jackmoon Threaded TUFF-Link Conduit Coupler, Size 1.20, for conduits with outer diameter between 41.70 and 42.70 mm, gray

- Designed for both press-on and thread-on airtight connections of smooth walled and ribbed HDPE duct and inner duct
- Features high tensile strength plastic with exceptional resistance to side load pressure for maximum durability
- Air-tight and water-tight coupling or splicing of conduits and inner ducts reduces cable pulling and blowing resistance
- Recommended that couplers are installed with the hydraulic coupling press

Product Classification

Brand	Jackmoon®
Product Type	Conduit coupler, threaded
Product Series	TUFF-Link

Dimensions

Conduit Outer Diameter, maximum	42.70 mm 1.68 in
Conduit Outer Diameter, minimum	41.70 mm 1.64 in
Nominal Size	1-1/4 in

General Specifications

Color	Gray
--------------	------

Material Specifications

Material Type	All plastic construction
----------------------	--------------------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

