



Lace-up Hoisting Grip for 1-1/4 in coaxial cable and elliptical waveguide 64

## Product Classification

**Product Type** Hoisting grip

## Dimensions

**Nominal Size** 1-1/4 in  
**Grip Length, minimum** 635.00 mm | 25.00 in  
**Leader Length, minimum** 203.20 mm | 8.00 in

## Electrical Specifications

**DTF Effect** 0.1 dB  
**Return Loss Effect** 0.1 dB

## General Specifications

**Hoisting Grip Type** Lace-up hoisting grip  
**Attachment Spacing Intervals** 61 m | 200 ft  
**Material Type** Stainless steel  
**Ordering Note** CommScope® standard product in the United States and Canada  
**Package Quantity** 1  
**Support Clamp** Not included  
**Tool Type** Hoisting grip

## Mechanical Specifications

**Pull Load Capacity** 900 lb

## Packed Dimensions

**Height** 5.7 cm | 2.3 in  
**Length** 23.5 cm | 9.3 in  
**Width** 23.5 cm | 9.3 in  
**Shipping Weight** 0.38 kg | 0.83 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Below Maximum Concentration Value (MCV)

