



Lace-up Hoisting Grip for 2-1/4 in and elliptical waveguide 37

Product Classification

Product Type Hoisting grip

Dimensions

Nominal Size 2-1/4 in
Grip Length, minimum 660.40 mm | 26.00 in
Leader Length, minimum 355.60 mm | 14.00 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Lace-up hoisting grip
Attachment Spacing Intervals 61 m | 200 ft
Material Type Stainless steel | Tin-coated bronze
Ordering Note CommScope® non-standard product
Package Quantity 1
Support Clamp Not included
Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 1160 lb

Packed Dimensions

Height 15.3 cm | 15.3 in
Length 15.3 cm | 15.3 in
Width 3.3 cm | 3.3 in
Shipping Weight 0.77 kg | 1.70 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

