

L2SGRIP



Support Hoisting Grip for 3/8 in coaxial cable

Product Classification

Product Type Hoisting grip

Dimensions

Nominal Size 3/8 in
Grip Length, minimum 101.60 mm | 4.00 in
Leader Length, minimum 152.40 mm | 6.00 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Support hoisting grip
Attachment Spacing Intervals 61 m | 200 ft
Installation Tool Required, not included
Material Type Stainless steel | Tin-coated bronze
Ordering Note CommScope® non-standard product
Package Quantity 1
Support Clamp Included
Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 350 lb

Packed Dimensions

Height 2.5 cm | 1.0 in
Length 12.7 cm | 5.0 in

L2SGRIP

Width 17.8 cm | 7.0 in
Shipping Weight 0.30 kg | 0.66 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

