



PIM-free Multifunction Adapter for SnapTak Hangers

- Snaps into 3/4" holes to provide 1 inch standoff
- Threads into 3/8" & 1/2" bolts & U-bolts to launch hangers
- Snaps between SnapTak hangers to provide 360 degree hanger rotation
- For patents see www.cs-pat.com

Product Classification

| | |
|---------------------|-----------|
| Brand | PIM-guard |
| Product Type | Adapter |

Dimensions

| | |
|---------------|--------------------|
| Height | 26.00 mm 1.02 in |
| Length | 29.00 mm 1.14 in |
| Width | 29.00 mm 1.14 in |

General Specifications

| | |
|-------------------------|---|
| Adapter Type | Stand-off adapter |
| Color | Black |
| Material Type | Engineered plastic |
| Ordering Note | CommScope® standard product in the United States and Canada |
| Package Quantity | 10 |

Mechanical Specifications

| | |
|---|--|
| Environmental Strength Capability | Double cable weight |
| Maximum Loading | Triple stack for hangers SSH-47, SSH-710, SSH-1014, SSH-1416 |
| Mounting | 1/2 in threads 3/4 in through hole 3/8 in threads |
| UV Resistance, minimum with no degradation | ≥1000 hours |
| Vibration Survival | ≥4 hours at resonant frequency |

Packed Dimensions

| | |
|------------------------|-------------------|
| Height | 17.0 cm 6.7 in |
| Length | 10.0 cm 3.9 in |
| Shipping Weight | 0.15 kg 0.33 lb |
| Width | 13.0 cm 5.1 in |

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

