MCG23RHDX-13MB



G23RHDX Monopole Sector Frame with spine extension for RRU Mounting, 13 ft x 2.88 in OD face pipes. Base Kit Only. No antenna pipes

- Extended spine for MCG23 RHDX mounts that decrease PIM from radio relocation
- · Increased versatility and stability
- · Updated frame provides higher loading
- More RRU mounting available, reducing need for additional mounts
- · Better load management
- · Less structure stress
- Can be used in combination with APEX RRU mounts

Product Classification

Product Type High capacity monopole sector frame

Product Series G2

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 0
Sectors, quantity 3

Dimensions

Face Width 3.962 m | 13 ft

Width 3,962.4 mm | 156 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

Stand-off Distance 1,066.8 mm | 42 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative



MCG23RHDX-13MB

Wind Rating Test Method

TIA/EIA-222

Packaging and Weights

Included Mounting hardware | Ring mounts (2) | Sector frames (3) | Stiff arm

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code