

FGSB-MSHS-H-CF



FiberGuide® Horizontal Straight Section with Center Divider, 4x24in, Black

Product Classification

| | |
|-----------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Straight section |
| Product Brand | FiberGuide® |
| Product Series | FGS |

General Specifications

| | |
|--------------|------------------|
| Color | Black |
| Orientation | Horizontal |
| Section Type | Straight section |

Dimensions

| | |
|-------------------|--------------------------------|
| Height | 101.6 mm 4 in |
| Width | 609.6 mm 24 in |
| Length | 1829 mm 72.008 in |
| System Dimensions | 102 mm x 610 mm (4 in x 24 in) |

Material Specifications

| | |
|---------------|---------------------------|
| Material Type | Engineering Thermoplastic |
|---------------|---------------------------|

Environmental Specifications

| | |
|-------------------------|--------------------------------|
| Flammability Rating | CSA S143 UL 2024 UL 94 V-0 |
| Halogen Characteristics | Blue Angel TCO '99 WEEE |
| Safety Standard | CSA UL |

Packaging and Weights

| | |
|-------------|----------------------|
| Weight, net | 6.523 kg 14.381 lb |
|-------------|----------------------|

FGSB-MSHS-H-CF

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

