

SA-4C



PIM-Guard® Four-Way Snap-in Stand-off Adapter has two slots for round member attachment and 3/8" holes for angle adapter integration. It includes four 3/4" holes for Snap-in hangers, supporting three 4-30mm or two 36-42mm cable stacks per hole

Product Classification

Product Type	Adapter
Product Brand	PIM-Guard®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Adapter Type	Stand-off adapter
Color	Black
Mounting	3/4 in through hole 3/8 in through hole Round member

Dimensions

Maximum Stack Height	3
Height	54.61 mm 2.15 in
Outside Width	40.132 mm 1.58 in
Outside Length	86.36 mm 3.4 in

Material Specifications

Material Type	Engineered plastic
---------------	--------------------

Mechanical Specifications

Maximum Loading	Double stack for hangers SSH-2630, SSH-3642 Triple stack for hangers SSH-411, SSH-1117
Vibration Survival	≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥1000 hours

SA-4C

Packaging and Weights

Height, packed	17 cm 6.693 in
Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in
Packaging quantity	10
Weight, gross	0.27 kg 0.595 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power