

# MC-FM4-24-278



4-sector Monopole 24" Stand-off Mount kit, 10 in to 30 in OD, includes (4) 2-7/8" OD x 96" pipe

## Product Classification

**Product Type** Stand-off mount

## General Specifications

**Mounting** Monopole, 254–762 mm (10–30 in) OD

**Pipe, quantity** 4

**Sectors, quantity** 4

## Dimensions

**Height** 2,438.4 mm | 96 in

**Face Width** 0 m | 0 ft

**Pipe Length** 2,438.4 mm | 96 in

**Mounting Diameter, maximum** 762 mm | 30 in

**Mounting Diameter, minimum** 254 mm | 10 in

**Pipe Outer Diameter** 73.025 mm | 2.875 in

**Stand-off Distance** 609.6 mm | 24 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Pipe mounts | Plain end pipes (4) | Ring mount | Stand-off arms

**Packaging quantity** 1

**Weight, net** 260.453 kg | 574.2 lb