

# PFP-PX-S2



Power Express Class 2 shelf, accommodates up to 2 modules of 8 SELV /Class 2 outputs, 1U

- Integrated chassis control and management with immediate detection of active module alarms
- Supports 1 or 2 8 port NEC Class 2/SELV power modules
- New 1 RU design for flexible deployments
- 1600 W/30 A system power
- Web based GUI and SNMP Management
- Alarm card, controller card, rectifier, and 8 port power module sold separately

Power Express Class 2 shelf for up to 16 NEC Class 2 circuits. Alarm card, Controller card and power modules sold separately

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Power supply subrack
<b>Warranty</b>	One year

## General Specifications

<b>Color</b>	White
<b>Rack Type</b>	19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	444.5 mm   17.5 in
<b>Depth</b>	285.75 mm   11.25 in

## Electrical Specifications

<b>Input Voltage Range</b>	100 to 240 Vac
<b>Electrical Safety Standard</b>	CSA C22.2 No. 60950-1-03   IEC 60950-1   UL
<b>Total Output Power</b>	1600 W

## Environmental Specifications

# PFP-PX-S2

---

<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Relative Humidity</b>	5%–95%, non-condensing
<b>Standards Compliance</b>	EN 61000-4-2 level 4   GR 1089, Issue 4

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Carton
<b>Weight, net</b>	2.948 kg   6.5 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
-----------------	--