

# FD3-AG432J00GCBP7



FDH 3000 Fiber Distribution Medium Cabinet, 432F distribution loaded, SC/APC, no splitters, single armor loose tube, 100 ft, 2x216F distribution cable assembly, 72F feeder

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

## General Specifications

Access	Front
Cable Type	Armored - Single Loose Tube
Color	Putty white
Distribution Cables, quantity	2
Distribution Ports, quantity	432
Fibers per Distribution Cable, quantity	216
Fibers per Feeder Cable, quantity	72
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	24

## Dimensions

Height	1,066.8 mm   42 in
Width	685.8 mm   27 in
Depth	457.2 mm   18 in
Cable Length	30.48 m   100 ft
Enclosure Size	Medium

## Material Specifications

Finish	Powder coated
Material Type	Aluminum

# FD3-AG432J00GCBP7

---

## Environmental Specifications

<b>Environmental Space</b>	Above ground
----------------------------	--------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

<b>Packaging Type</b>	Pallet
-----------------------	--------