

# 760258674 | FMS-K2BA-L1A1-48-SP-DIN



FMS Fiber Optic Panel, 1U, 19 in, black, Includes 24 x LC SM Duplex Adaptors (48F), 48 x SM LC Pigtails. 48 x Splice protectors. Splice tray (2) and cable glands

## Product Classification

<b>Regional Availability</b>	DACH countries
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	FMS
<b>Ordering Note</b>	Specific panel MID according to local requirements in DACH region

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Body Style</b>	Symmetrical
<b>Cable Exit Location</b>	Rear, left side
<b>Color</b>	Black
<b>Interface, front</b>	LC/UPC
<b>Fiber Color Code</b>	DIN VDE 0888
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding
<b>Splice Trays Included, quantity</b>	2
<b>Splicing Type</b>	Heat shrink, single fiber fusion
<b>Total Ports, quantity</b>	48

## Dimensions

<b>Height</b>	44.3 mm   1.744 in
<b>Width</b>	482.2 mm   18.984 in
<b>Depth</b>	344.2 mm   13.551 in

## Material Specifications

# 760258674 | FMS-K2BA-L1A1-48-SP-DIN

---

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A1

**Insertion Loss, maximum** 0.3 dB

**Return Loss, minimum** 45 dB

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

