

MCG22HDX15-15-WLL



G22HDX Monopole Sector Frame with extended face, 15 ft x 2.88 in OD face pipes. Includes fifteen 2.88 OD x 120 in antenna pipes

Product Classification

Product Type	High capacity monopole sector frame
Product Brand	PIM-guard
Product Series	G2

General Specifications

Mounting	Monopole, 381–1270 mm (15–50 in) OD
Pipe, quantity	15
Sectors, quantity	3

Dimensions

Face Width	4.572 m 15 ft
Width	4,572 mm 180 in
Face Support Pipe Diameter	73.025 mm 2.875 in
Mounting Diameter, maximum	1270 mm 50 in
Mounting Diameter, minimum	381 mm 15 in
Pipe Outer Diameter	73.025 mm 2.875 in
Stand-off Distance	1,066.8 mm 42 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Included	Mounting hardware Plain end pipes Ring mounts (2) Sector frames (3) Stiff arm
-----------------	---

MCG22HDX15-15-WLL

Packaging quantity 1
Weight, net 1,153.853 kg | 2,543.81 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

