## 760126151 | P-004-DZ-CM-FSUAQ/8W002/5L002



Fiber indoor cable, TeraSPEED® Fiber Plenum Distribution, interlocking aluminum armored with plenum jacket, singlemode/multimode, aqua, 4 fiber single-unit, Feet jacket marking, Aqua jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

Feet

Portfolio CommScope®

**Product Type** Fiber indoor cable

**Product Series** P-DZ

General Specifications

Armor Type Interlocking aluminum

Cable Type Distribution

Construction Type Armored

**Subunit Type** Gel-free

Jacket Color Aqua

\_

Composite Fiber Count 2 + 2

Total Fiber Count 4

**Dimensions** 

**Jacket Marking** 


 Diameter Over Armor
 10.8 mm | 0.425 in

 Diameter Over Jacket
 12.8 mm | 0.504 in

Representative Image



# 760126151 | P-004-DZ-CM-FSUAQ/8W002/5L002



### Mechanical Specifications

Minimum Bend Radius, loaded192 mm7.559 inMinimum Bend Radius, unloaded128 mm5.039 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbf

 Compression
 85 N/mm | 485.363 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 35 N-m | 309.776 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 148 m | 485.564 ft

Optical Specifications

Fiber Type Composite MM/SM | G.652.D and G.657.A1, TeraSPEED® | OM3, LazrSPEED® 300

## **Environmental Specifications**

**Installation temperature** 0 °C to +70 °C (+32 °F to +158 °F)

Page 2 of 3

# 760126151 | P-004-DZ-CM-FSUAQ/8W002/5L002

**Operating Temperature**  $-20 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C } (-4 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$ 

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFCP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

### **Environmental Test Specifications**

**Heat Age**  $-20 \, ^{\circ}\text{C} \text{ to } +85 \, ^{\circ}\text{C} \, (-4 \, ^{\circ}\text{F to } +185 \, ^{\circ}\text{F})$ 

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-20 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F}\right)$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 138 kg/km | 92.732 lb/kft

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



#### Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

CS-8W-TB - TeraSPEED® Singlemode Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

