

# 760258355 | PPL-FA-4U-VCM

---



Propel 4RU front access fiber panel with cable trough for Propel XFrame. Accepts 24, 12 fiber Propel ULL modules, splice cassettes or 6 port adapter packs

- Panel comes with 24 carriers to allow for all front access using standard Propel components. Incoming cable and patch cords are routed at the front of the panel
- VCM (Vertical Cable Management) panels: With VCM panels, patch cords are routed straight down to a trough and over. This provides finger access for Moves, Adds and Changes
- For use with 12 fiber Propel components

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Color</b>	Gray
<b>Interface, front</b>	Unloaded
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	4
<b>Shelf Movement</b>	Fixed

## Dimensions

<b>Height</b>	178 mm   7.008 in
<b>Width</b>	483 mm   19.016 in

## Material Specifications

<b>Material Type</b>	Aluminum   Steel
----------------------	------------------

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## Packaging and Weights

**Packaging quantity** 1  
**Weight, net** 5.126 kg | 11.3 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

