

CSC7-D5A1A1CA000



NOVUX™ CSC200 Compact Fiber Closure, splice only, 6 single fiber trays with island for ANT splice protectors, 4 feeder ports, no adapters, no splitters, with mounting bracket, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	CSC 200

General Specifications

Cable Ports Quantity, total	4 round ports + 12 multi-out ports (24 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Pole Wall
Port, quantity	0
Splice Tray Included, quantity	6
Splice Tray Type Included	24-way, single fiber slim trays with island
Splicing Capacity, maximum	144
Splitter Type	No splitter
Splitter, quantity	0

CSC7-D5A1A1CA000

Dimensions

Height	388.2 mm 15.283 in
Width	222 mm 8.74 in
Depth	116 mm 4.567 in

Environmental Specifications

Environmental Space	Outdoor
UV Resistance	UV stabilized

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1
Packaging Type	Box Carton