

# 760259590 | PPL-DM-12AP-12LC-SM-BEU



Propel ULL Singlemode MPO-12 Distribution Module, 6 duplex LC/UPC to 1X12f MPO/APC pinned, Method B Enhanced

- Ultra-low loss (ULL) with Method B Enhanced polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 3 of the 12 lanes on the Propel Panel blade

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Functionality</b>	Breakout
<b>Color, front</b>	Blue
<b>Color, rear</b>	Gray
<b>Interface, front</b>	LC/UPC
<b>Interface Feature, front</b>	Internal shutters
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	APC   Internal shutters   Key up/up   Pinned
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Total Fibers, quantity</b>	12
<b>Total Ports, quantity, front</b>	6
<b>Total Ports, quantity, rear</b>	1

## Dimensions

<b>Height</b>	11 mm   0.433 in
<b>Width</b>	98 mm   3.858 in
<b>Depth</b>	170 mm   6.693 in

## Optical Specifications

# 760259590 | PPL-DM-12AP-12LC-SM-BEU

---

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2
<b>Insertion Loss, maximum</b>	0.6 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
<b>Safety Standard</b>	c-UL-us

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---