760260285 | BUDI-FS32-ADPSL



BUDI™ Fiber Optic Wall mount Enclosure with FOSC Management System, 36 SC/APC Sliding Adapters, (1) pre-terminated pigtail

- Compact, wall mountable fiber enclosures for indoor and outdoor use
- Specifically designed for fast FTTH deployment and easy customer connection
- Available with splicing (FIST) and/or patching and/or splitter combinations
- Multiple and modular wrap around cable port sealing options

Product Classification

Regional AvailabilityNorth AmericaPortfolioCommScope®Product TypeFiber wall box

Product BrandBUDI™Product SeriesBUDI-FSCountry Specific forUnited States

Warranty For more information, please consult our Product Warranty guidelines

General Specifications

Functionality Patching | Splicing

Access Front
Adapter Packs Included, quantity 36
Adapter Ports, quantity 32
Adapters, quantity 32
Enclosure Color Gray

Front Cover Type Snap-on cover

InterfaceSC/APCMountingWallSplicing Capacity, maximum36

Dimensions

 Height
 425 mm | 16.732 in

 Height, with cover
 500 mm | 19.685 in


 Width
 295 mm | 11.614 in



760260285 | **BUDI-FS32-ADPSL**

Depth 145 mm | 5.709 in

Dimension Drawing



Material Specifications

Enclosure Material Type LSZH thermoplastic

Environmental Specifications

Indoor/Outdoor **Environmental Space**

Flammability Rating UL 94 V-0

Qualification Standards IEC 60529, IP54 | IEC 61753-1, category G

Packaging and Weights

Agency

Included Cable seal | Pigtail seals | Splice tray

Packaging quantity

Packaging Type Box | Carton

Regulatory Compliance/Certifications

CHINA-ROHS

Above maximum concentration value

Classification

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

Page 2 of 3

760260285 | BUDI-FS32-ADPSL

UK-ROHS

Compliant/Exempted



* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines

