



## BTTF Faceplate only, for BTTF2-7Q RF Tap

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

- Support expanded bandwidth up to 1218 MHz
- Enable Cable Wi-Fi® Access Point powering via the F-port
- Improve network performance with signal conditioning plug-ins
- High quality RF connection with auto-seize F-connectors
- Maintain existing install base with compatibility back to “F” series FFT housings
- High level of network resilience with 6 kV surge resistance
- Maintain RF and AC continuity with integrated bypass capability

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Faceplate for tap
<b>Product Series</b>	BTTF
<b>Government Requirements</b>	Build America Buy America (BABA) compliant*

## General Specifications

<b>Location of Manufacturing</b>	Waived per BABA waiver for BEAD Program
<b>Number of Ports</b>	2

## Dimensions

<b>Height</b>	114.3 mm   4.5 in
<b>Depth</b>	88.9 mm   3.5 in
<b>Length</b>	139.7 mm   5.5 in

## Electrical Specifications

<b>Bandwidth</b>	5 – 1218 MHz
<b>Insertion Loss, tap, nominal</b>	7 dB
<b>Power Passing at 60/90V, maximum</b>	12 A
<b>Surge Protection, F port</b>	6 kV Combination Wave

## Environmental Specifications

**Operating Temperature** -40 °C to +60 °C (-40 °F to +140 °F)  
**Standards Compliance** IEC 60950-22 edition 2.0 2016-01

## Packaging and Weights

**Weight** 0.68 kg | 1.5 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

