



REGAL RLS 1.2 GHz RF splitter, 3 unbalanced outputs, AC power#passing

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

- Support DOCSIS® 3.1 expanded bandwidth up to 1218 MHz
- Maintain existing Regal installed base with compatible faceplate upgrades
- Easily configured to enable or block AC power as needed in the network
- Faceplate only options for cost-effective upgrades to existing Regal deployments
- Support aerial or pedestal installation with flexible design
- Protect valuable network equipment investment with heavy surge suppression options available

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Splitter
Product Series	REGAL
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Location of Manufacturing	Waived per BABA waiver for BEAD Program
---------------------------	-----------------------------------------

Dimensions

Height	116.84 mm 4.6 in
Depth	76.2 mm 3 in
Length	139.7 mm 5.5 in

Electrical Specifications

Current Handling, ac ports	20 A
Current Handling, RF ports	15 A
Operating Frequency Band	5 – 1218 MHz
Surge Protection	No

Environmental Specifications

Operating Temperature

-40 °C to +60 °C (-40 °F to +140 °F)

Packaging and Weights

Weight

0.68 kg | 1.5 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

