



G2 Splice Cassette, 24LC/APC with internal shutters, OS2, with 250um pigtails

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Series	G2

## General Specifications

Color, front	Green
Interface, front	LC/APC
Interface, rear	Stranded pigtail
Polarity	Pairs, straight
Shuttered	Yes
Total Fibers, quantity	24

## Dimensions

Height	26.416 mm   1.04 in
Width	96.52 mm   3.8 in
Depth	165.354 mm   6.51 in

## Material Specifications

Alignment Sleeve Material	Zirconia
---------------------------	----------

## Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.4 dB
Return Loss, minimum	60 dB

### Environmental Specifications

Qualification Standards	IEC 61753-1   TIA-568.3-D
Safety Standard	UL

### Packaging and Weights

Included	SMOUV holder   SMOUV splice protection
Packaging quantity	1
Weight, net	0.147 kg   0.324 lb

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

