

760258205 | G2-SP-24LC-OM4-PT-BE



G2 Splice Cassette, 24LC with internal shutters, OM4, with 250um pigtails, Method B Enhanced

For use in applications when End B of the cable is connectorized with an MPO that connects into a module with Method B Enhanced polarity

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Series	G2

General Specifications

Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Polarity	Method B Enhanced
Shuttered	Yes
Total Fibers, quantity	24

Dimensions

Height	26.416 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	165.354 mm 6.51 in

Material Specifications

Alignment Sleeve Material	Zirconia
---------------------------	----------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4
Insertion Loss, maximum	0.15 dB
Return Loss, minimum	35 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	UL

Packaging and Weights

Included	SMOUV holder SMOUV splice protection
Packaging quantity	1
Weight, net	0.147 kg 0.324 lb