

# FGSB-MHRT-F/H



FiberGuide® Horizontal T, 4x12in, 4x14in Exit, Black

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Tee
Product Brand	FiberGuide®
Product Series	FGS

## General Specifications

Product Feature	Transition
Color	Black
Orientation	Horizontal
Section Type	Tee section

## Dimensions

Height	114.046 mm   4.49 in
System Dimensions	102 mm x 305 mm (4 in x 12 in)   102 mm x 610 mm (4 in x 24 in)

## Ordering Tree

# FGSB-MHRT-F/H

9

FGS

B

-

MHRT

-

H

10

Section Color

9

empty

yellow

B

black

Section Size

10

A

4 x 4 in

B

4 x 6 in

B-VS

4 x 6 in, variable support bracket

F

4 x 12 in

F/B

4 x 12 in, 6 in exit

F/B-S

4 x 12 in, 6 in exit, with variable support bracket

F/B-VS

4 x 12 in, 6 in exit, variable support bracket

F-VS

4 x 12 in, variable support bracket

G

2 x 6 in

H

4 x 24 in

H/F

4 x 24 in, 12 in exit

H/F-VS

4 x 24 in, 12 in exit, variable support bracket

M

4 x 18 in

M/F

4 x 18 in, 12 in exit

M/H

4 x 18 in, 24 in exit

H/M

4 x 18 in

\* Support brackets only come in black

## Material Specifications

**Material Type**                      Engineering Thermoplastic

## Environmental Specifications

**Flammability Rating**                      CSA S143   |   UL 2024   |   UL 94 V-0

**Halogen Characteristics**                      Blue Angel   |   TCO '99   |   WEEE

**Safety Standard**                      CSA   |   UL

## Packaging and Weights

**Weight, net**                      1.338 kg   |   2.95 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



