



Constellation Rackmount FMP Receiver with power service outlets in 110 VAC, 48 VDC, and 24 VDC form

Product Classification

Regional Availability	North America
Portfolio	SYSTIMAX®
Product Type	Backplane
Product Brand	Constellation™

General Specifications

Color	Putty white
-------	-------------

Dimensions

Height	256 mm 10.079 in
Width	560.8 mm 22.079 in
Depth	166.8 mm 6.567 in

Electrical Specifications

Output Power, maximum	1 kW
Output Voltage	48 Vdc

Material Specifications

Material Type	Aluminum
---------------	----------

Environmental Specifications

Operating Temperature	-20 °C to +50 °C (-4 °F to +122 °F)
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing
Environmental Space	Indoor
Safety Standard	IEC 62368-1

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

