


FGSB-MDSP-M



FiberGuide® Downspout, 4x18in, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Downspout
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Downspout

Dimensions

Height	210 mm 8.268 in
Width	498 mm 19.606 in
Length	380 mm 14.961 in
System Dimensions	102 mm x 457 mm (4 in x 18 in)

Ordering Tree

FGSB-MDSP-M



Section Color

9	empty	yellow
	B	black

Section Size

10	2B	4 x 6 in, 4 x 4 in dual drop
	A	4 x 4 in
	A/I	4 x 4 in, insertable
	B	4 x 6 in, 4 x 4 in drop
	B/I	4 x 6 in, insertable
	C	2 x 2 in, extended
	EX-	extended
	F	4 x 12 in, 4 x 6 in drop
	F/I	4 x 12 in, 4 x 6 in drop, insertable
	G	2 x 6 in, 2 x 2 in drop
	IMP	4 x 6 in, dual drop with divider
	M	4 x 18 in

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 1.788 kg | 3.942 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



