F042BBS1



FlexTwist® Flexible Twist for WR42, 17.7–26.5 GHz, with interface types UG-595/U and UG-595/U, 300 mm

Product Classification

Product Type Rectangular waveguide, flexible twist

Product Brand FlexTwist®

General Specifications

ComponentFlexible TwistInterfaceUG-595/UInterface 2UG-595/U

Dimensions

 Length
 300 mm | 11.811 in

 Waveguide Size
 WR42 | WG20 | R220

Electrical Specifications

Attenuation 2.62 dB/m | 0.799 dB/ft

Average Power 100 W

Operating Frequency Band 17.7 – 26.5 GHz

 Peak Power
 39 kW

 VSWR
 1.2

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)38 mm | 1.496 inMinimum Bend Radius, Multiple Bends (H Plane)76 mm | 2.992 in

 Maximum Twist
 510 °/m | 155.448 °/ft

 Pressurization, maximum
 0.31 N/mm² | 45 psi



F042BBS1

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

