

F062BBS5



FlexTwist® Flexible Twist for WR62, 12.4–18.0 GHz, with interface types UG-419/U and UG-419/U, 1200 mm

Product Classification

| | |
|---------------|---------------------------------------|
| Product Type | Rectangular waveguide, flexible twist |
| Product Brand | FlexTwist® |

General Specifications

| | |
|-------------|----------------|
| Component | Flexible Twist |
| Interface | UG-419/U |
| Interface 2 | UG-419/U |

Dimensions

| | |
|----------------|---------------------|
| Length | 1200 mm 47.244 in |
| Waveguide Size | WR62 WG18 R140 |

Electrical Specifications

| | |
|--------------------------|-------------------------|
| Attenuation | 0.99 dB/m 0.302 dB/ft |
| Average Power | 400 W |
| Operating Frequency Band | 12.4 – 18.0 GHz |
| Peak Power | 100 kW |
| VSWR | 1.3 |

Mechanical Specifications

| | |
|---|------------------------|
| Minimum Bend Radius, Multiple Bends (E Plane) | 52 mm 2.047 in |
| Minimum Bend Radius, Multiple Bends (H Plane) | 102 mm 4.016 in |
| Maximum Twist | 445 °/m 135.636 °/ft |
| Pressurization, maximum | 0.31 N/mm² 45 psi |

F062BBS5

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.andrew.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

