

F062BMS3



FlexTwist® Flexible Twist for WR62, 12.4–18.0 GHz, with interface types UG-419/U and UBR140, 900 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	UG-419/U
Interface 2	UBR140

Dimensions

Length	900 mm 35.433 in
Waveguide Size	WR62 WG18 R140

Electrical Specifications

Attenuation	0.99 dB/m 0.302 dB/ft
Average Power	400 W
Operating Frequency Band	12.4 – 18.0 GHz
Peak Power	100 kW
VSWR	1.1

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	52 mm 2.047 in
Minimum Bend Radius, Multiple Bends (H Plane)	102 mm 4.016 in
Maximum Twist	445 °/m 135.636 °/ft
Pressurization, maximum	0.31 N/mm² 45 psi

F062BMS3

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system