

F062KMS2



FlexTwist® Flexible Twist for WR62, 12.4–18.0 GHz, with interface types PBR140 and UBR140, 600 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	PBR140
Interface 2	UBR140

Dimensions

Length	600 mm 23.622 in
Waveguide Size	WR62 WG18 R140

Electrical Specifications

Attenuation	0.99 dB/m 0.302 dB/ft
Average Power	400 W
Operating Frequency Band	12.4 – 18.0 GHz
Peak Power	100 kW
VSWR	1.1

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	52 mm 2.047 in
Minimum Bend Radius, Multiple Bends (H Plane)	102 mm 4.016 in
Maximum Twist	445 °/m 135.636 °/ft
Pressurization, maximum	0.31 N/mm² 45 psi

F062KMS2

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

